Cartridge

308 Norma Mag - 200 grain

Version 9.0

105%





300 Norma Mag 200				grain		30 Call (.300)		
MAXIMUM O.A.C.L.				3.347"		E	3.C.	S.D.
AccuBond® AB			200gr. Spitzer		C).588	0.301	
Partition® PT			200gr. Spitzer		C	.481	0.301	
CASE TYPE: Norma				PRIMER TYPE		Fed 215		
CASE HOLDS:	66.7 Gr. WATER			BARREL Length/Make		24" Wiseman		
				BARREL Twist			1-10"	
POWDER TYPE	POWDER CHG. GRS.			MUZZLE VEL. F.P.S.			LOAD DENSITY (VOLUME)	
IMR 4895	54.0	* MAX.	2603					88%
	52.0		2547					85%
	50.0		2492					82%
IMR 4320	56.0	MAX.	2610					91%
	54.0		2550					88%
	52.0	*	2490					85%
IMR 4350	66.0	* MAX.	2740			*		106%
	64.0		2640			*		103%
	62.0		2540					99%
N165	67.0	MAX.	2747					112%
Most Accurate	65.0		2678				•	108%
Powder Tested	63.0	*	2608			**		105%
IMR 4831	69.0	* MAX.	2760			*1	• .	111%
	67.0		2690			*1	• .	107%
	65.0		2620			*	• .	104%
H4831	68.0	* MAX.	2822			*	•	106%
	66.0		2757			*	*	103%
	64.0		2692					100%
RL22	68.5	MAX.	2850			*	•	I12%
	66.5		2768			*	•	108%

All cartridge measurements are SAAMI maximum and due to variations from manufacturers actual measurements may vary * Because Nosler, Inc. has no control over the actual components selected, the manner in which they are assembled or the

2685

64.5

condition of the firearm used, no responsibility, either expressed or implied is assumed for the use of this data. In no event shall Nosler, Inc. be liable for any damages resulting from the use of this data."

^{* =} Most accurate load tested

^{** =} Compressed load